

# ILA.PIV.sCMOS CLHS Camera



The ILA.PIV.sCMOS CLHS is our flagship when your application is tough and demands are high:

- interframing time as low as 120 ns
- New CamLink HS:
  - Effective bandwidth of nearly 1,2 GB/s
  - Cable length up to 10 km possible
- 16 bit dynamic range
- >60% quantum efficiency

Now, you are prepared for every PIV task at hand.

To facilitate camera setup a remote focus control is directly integrated.

Adjust your Canon EF lens precisely via our intuitive software without the need to access the camera anymore.

Data Sheet

ILA\_5150 GmbH  
Kurbrunnenstraße 24  
52066 Aachen - Germany  
Fon +49(0)241 95789-814  
Fax +49(0)241 95789-585  
[info@ila5150.de](mailto:info@ila5150.de) [www.ila5150.de](http://www.ila5150.de)



# ILA.PIV.sCMOS CLHS Camera

## General


power supply	12..24 VDC ( $\pm 10\%$ )
power consumption	32 W max. (typ. 19W @ 20 °C)
weight	1000 g
operating temp.	+10 °C .. +40 °C
operating humidity	10% .. 80% (non-condensing)
storage temp range	-10 °C .. +60 °C
optical interface	Canon EF lens mount*
CE / FCC certified	yes

\* F-mount available upon request

## Frame rate table<sup>3</sup>

Typical resolution	rs	gs
2560 x 2160	100	50
2560 x 1024	212	105
1920 x 1080	201	100

## Quantum efficiency [%]



<sup>1</sup> The readout noise values are given as median (med) and root mean square (rms) values, due to the different noise models, which can be used for evaluation.

<sup>2</sup> Raw data without filtering.

<sup>3</sup> Max. fps with centered ROI.

<sup>4</sup> The high dynamic signal is simultaneously converted at high and low gain by two 11 bit A/D converters and the two 11 bit values are sophisticatedly merged into one 16 bit value

## Image Sensor

type of sensor	scientific CMOS (sCMOS)
image sensor	CIS2521
resolution (h x v)	2560 x 2160 pixel
pixel size (h x v)	6.5 $\mu\text{m}$ x 6.5 $\mu\text{m}$
sensor size	16.6 mm x 14.0 mm
diagonal	21.8 mm
shutter modes	Rolling (rs) and global (gs)
dynamic range	30 000 : 1 (86.9 dB)
quantum efficiency	>60% @ peak
spectral range	370 nm .. 1100 nm
anti blooming factor	>10 000
MTF	76.9 lp/mm (theoretical)
fullwell capacity	30 000 e <sup>-</sup>
readout noise <sup>1</sup>	2.5 <sub>rms</sub> / 2.2 <sub>med</sub> e <sup>-</sup> @ (gs, fsc <sup>2</sup> )
dark current <sup>4</sup> @ 7 °C	< 0.6 e <sup>-</sup> /pixels/s (rs) < 0.9 e <sup>-</sup> /pixels/s (gs)
DSNU	< 3.9 e <sup>-</sup> rms (gs, fsc <sup>2</sup> )
PRNU	< 0.34%

## Camera

frame rate	100fps @ 2560 x 2610 pixel (rs, fsc <sup>2</sup> ) 50fps @ 2560 x 2160 pixel (gs, fsc <sup>2</sup> )
exposure / shutter time	500 $\mu\text{s}$ .. 2 s (rs) 10 $\mu\text{s}$ .. 100 ms (gs)
interframing time	as low as 120 ns
dynamic range A/D <sup>2</sup>	16 bit
A/D conversion factor	0.46 e <sup>-</sup> /count
pixel scan rate	286 MHz (fsc <sup>2</sup> )
pixel data rate	572 Mpixel/s
region of interest	Selectable in steps of 16 hor / 1 vert Px
non linearity	< 0.6%
cooling method	Peltier with forced air (fan); +7°C stabilized up to 27°C ambient
trigger input signals	frame or sequence trigger
trigger output signals	exposure, busy
data interface	Camera Link HS (Single-F2,1X1,S10)